

**Garant**
**Arbor for screw-in milling cutters with thread vibration-damped, tapered form, HSK-A 63, Thread M×length L1: M12X150**

**Order data**

Order number	307037 M12X150
GTIN	4045197905130
Item class	31A

**Description**
**Version:**

With RFID/Balluffchip bore. Tapered design. **Vibration damped version, arbor with vibration-damping core.**

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Extensions No. 301342, reducers No. 301344, coolant tube No. 309880, coolant tube socket wrench No. 309890.

**Note:**

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

**Technical description**

Ø D <sub>2</sub>	21 mm
Overhang dimension A	176 mm
Reach L <sub>1</sub>	150 mm
Bore Ø D <sub>1</sub>	12.5 mm
Thread M	M12×150
External Ø D	40 mm

L <sub>2</sub>	5 mm
Adapter	HSK-A 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor