

Rigid load arm, Base length in m / safe working load in t: 2,4/2,5



Order data

| | |
|--------------|----------------|
| Order number | 919973 2,4/2,5 |
| GTIN | 4052462012813 |
| Item class | 94B |

Description

Version:

Load arms increase the reach of the fork-lift truck. Sturdy steel construction with fork insertion slots for fork tines. Also suitable for clamp trucks. Chain protection against accidental slippage and a swivel hook. Rigid design with 3 available hook positions.

Colour:

Optional **paint finishes** RAL 5012, Light blue, RAL 2000 Yellow orange, RAL 3000 Fire red, RAL 6011 Reseda green, RAL 7005 Mouse grey.

Note:

Comply with the load capacity of the fork lift truck!

Technical description

| | |
|--------------------------------------|----------------------------------|
| Width | 600 mm |
| Base length | 2400 mm |
| Internal dimension at intake: width | 220 mm |
| Load capacity of the outermost eye | 250 kg |
| maximum load capacity | 2500 kg |
| Weight | 88 kg |
| Internal dimension at intake: height | 80 mm |
| Fork-lift fork socket pitch | 160 mm |
| Colour selection | RAL 5012, 2000, 3000, 6011, 7005 |

Type of product

Load arm