

Telescopic load arm, Base length in m / safe working load in t: 1,6/1**Order data**

Order number	919974 1,6/1
GTIN	4052462012936
Item class	94B

Description**Version:**

Load arms increase the reach of the fork-lift truck. Sturdy steel construction with fork insertion slots for fork tines. Also suitable for clamp trucks. Chain protection against accidental slippage and a swivel hook. Telescopic with 7 available hook positions. Can be locked in any position with studs. Angle of inclination 25°. With support legs, access height 100 mm.

Colour:

Optional **paint finishes** RAL 5012, Light blue, RAL 2000 Yellow orange, RAL 3000 Fire red, RAL 6011 Reseda green, RAL 7005 Mouse grey.

Note:

Comply with the load capacity of the fork lift truck!

Technical description

Width	600 mm
Base length	1600 mm
Length, extended	2500 mm
Internal dimension at intake: width	220 mm
Load capacity of the outermost eye	125 kg
maximum load capacity	1000 kg
Weight	55 kg

Internal dimension at intake: height	80 mm
Fork-lift fork socket pitch	160 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Load arm