

ALLURIS

FMI-B20 Digital peak force gauge, Measuring range: 500N**Order data**

Order number	478983 500
GTIN	4260244680567
Item class	47F

Description**Version:**

- **Sturdy force gauges in a handy aluminium die-cast housing for compressive and tensile forces from 0.001 to 2500 N.**
- **Overload protection up to 500% and protected measurement shaft.**
- **Attachment thread for additional handles.**
- **Precise positioning in test stands by a guide pin.**
- **High measurement rate for precise recording of peak values to determine fracture or tearing forces.**

Advantage:

Operating time up to 150 h without mains power thanks to the rechargeable LiPo battery.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Measurement of compressive and tensile forces in quality assessment and production. For use as a mobile manual measurement gauge both in outdoor areas and in test stands or jigs. Attachment thread integrated into the housing permit attachment in test stands or mounting of additional handles.

Supplied with:

Force gauge in a protective case. Screw-on accessories for force transfer (flat head, slot head, cone, hook). Quick-start instructions.

Technical description

Measuring range	500 N
Resolution	0.1 N
IP Index of Protection	IP 65
Length	150 mm
Height	29 mm
Width	82 mm
Error limit	±0.2 maximum value (±1 digit) %
Connection thread	M6
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Measurement technology	digital
Calibration	Price on request
Type of product	Draw bar pulling force gauge