

Flat scissor lift table, Load capacity kg / model: 1000/1



Order data

| | |
|--------------|---------------|
| Order number | 919991 1000/1 |
| GTIN | 4053981010991 |
| Item class | 08Y |

Description

Version:

Sturdy bracing struts with a platform made of smooth steel plate. For the stepless lifting and lowering of loads, goods on pallets, mesh crates and for height adjustment when materials are being transferred to machines. For use on an industrial floor without excavation of foundations, extremely low profile. Reliable and safe operation by push button with the functions on/off in a dead man's circuit and emergency stop. Overload protection by integral pressure limitation valve. Optimum safety in operation and maintenance due to integral pipe failure valve and maintenance spigots. Drive-on ramp permits the use of the height-adjustable workbench with a fork-lift truck or transport truck.

Standard:

DIN EN 1570-1; EG-Maschinenrichtlinie 2006/42/EG und UVV-Vorschriften.

Note:

- **Ambient indoor temperature range from 0 °C to 40 °C.**
- **Before commissioning, the installation and electrical connections should be checked by an expert.**
- **Check the existing load-bearing characteristics of the ground in relation to the overall weight of the lift table.**

Technical description

| | |
|-------------------|---------|
| Width | 1140 mm |
| Safe working load | 1000 kg |
| Weight | 250 kg |

| | |
|-------------------|--------------------|
| Overall height C | 82 mm |
| Lift height H | 760 mm |
| Lift time | 18 s |
| Length L | 1450 mm |
| AC supply voltage | 400 V |
| Mains frequency | 50 Hz |
| Power supply | Mains operated |
| Type of product | Scissor lift table |