



## Fine stoneware drill /tiles drill, Drill Ø: 5mm



### Order data

Order number	787035 5
GTIN	9002741169054
Item class	76G

### Description

#### Version:

2 pieces. A drill with a **diamond-ground carbide tip** with a patented centring tip for highly accurate start positioning and exact holes without break-outs. With 10 mm shank. A carbide drill for use in standard drill chucks. With 1/4 inch (E 6.3) hexagon shank.

#### Application:

For **very hard stoneware tiles** up to Mohs / scratch hardness class 9 and for glass and porcelain.

#### Note:

Not suitable for hammer drills. Maximum spindle speed 200 rpm. No cooling required.

### Technical description

Use with impact / without impact	not for impact drilling
Shank	Plain shank
maximum speed	200 min <sup>-1</sup>
overall length	105 mm
Number of drills	2

Bit hexagon shank	E 6,3
Drill Ø	5 mm
Shank Ø	10
Tool material	Carbide
Type of product	Masonry drill