



## Pair of gloves KX-01A SHADOW, Glove size: 9



### Order data

|              |               |
|--------------|---------------|
| Order number | 094312 9      |
| GTIN         | 6942542967950 |
| Item class   | 02H           |

### Description

#### Version:

Extremely close-fitting and light-weight safety gloves with very high breathability. Very high comfort and pleasant sensation when wearing, for versatile applications in the field of precision mechanics.

- **Very thin (0.55 mm), hand-sewn backing material with long working life.**
- **Breathable wavex grip structure on the palms and fingers for a butter grip and optimum product safety.**
- **Backs of hands of reinforced Lycra for greater freedom of movement.**
- **Suitable for touch screens.**

#### Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Glove characteristics: Free of latex

Colour: black / grey

### Technical description

|            |    |
|------------|----|
| Glove size | 9  |
| Series     | KX |

|                       |  |
|-----------------------|--|
| Type of glove         | Multi-purpose gloves   |
| Protection category   | Category II  |
| Contents              | 1  |
| Washing               | 40 °C coloureds  |
| Drying                | air dry  |
| Glove characteristics | DMF-free   |
| Glove characteristics | Reinforced crook of the thumb                                  |
| Glove characteristics | Suitable for touch screens                                     |
| Glove characteristics | free of latex  |
| EN 388:2016           | 2111X  |
| Backing material      | Synthetic leather/Spandex                                      |
| Coating variant       | The palms of the hands   |
| Application range     | Precision  |
| Length                | 240 mm   |
| Colour                | black / grey   |
| AQL                   | G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor. |
| Application           | reusable   |
| Type of product       | Multi-purpose gloves   |