

Ansell**Pair of gloves HyFlex® 11-937, Glove size: 7****Order data**

Order number	094486 7
GTIN	10076490449770
Item class	04P

Description**Version:**

HyFlex® 11-937. Lightweight glove with a very good combination of cut protection, oil repellency and increased durability. Double coating of polyurethane and nitrile foam for a secure grip. With **18-gauge knitted fabric** and Dyneema® Diamond technology fibres.

Version of the advertising text:

HyFlex® 11-937. Lightweight glove with a very good combination of cut protection, oil repellence and increased durability.

- **Double coating of polyurethane and nitrile foam for a secure grip.**
- **With 18-gauge knitted fabric and Dyneema® Diamond technology fibres.**
- **For use when performing precision work.**
- **Colour: grey/black**

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof

Technical description

Glove size	7
Series	HyFlex®
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
Glove characteristics	DMF-free
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	Silicone-free
Knitted technology	18G
Clothing standard	Oeko-Tex Standard 100
EN 388	4X42B
Backing material	Dyneema®
Coating	PU/nitrile foam
Material	Nitrile foam
Coating variant	3/4 coating
Application range	Precision
Colour	grey / black
Weight	28 g
Length	212 mm
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves