

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	260320 12/07
GTIN	4045197877703
Item class	21T

Technical description

ISO code toolholder	E12M SDQCR/L07
Overall length L	150 mm
Centre offset L ₃	8.5 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	16 mm
Insert size	7 mm
Clamping height L ₂	11.6 mm
suitable indexable insert	DC.. 0702..
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	12 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500