

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	260320 20/11
GTIN	4045197877727
Item class	21T

Technical description

Clamping height L_2	18.9 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Centre offset L_3	12.5 mm
Insert size	11 mm
Setting angle κ	107.5 degrees
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Overall length L	250 mm
ISO code toolholder	E20S SDQCR/L11
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500