

Garant
Open ended spanner / ratchet ring spanner, Width across flats: 30mm

Order data

Order number	614800 30
GTIN	4045197286086
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 425 mm

Jaw width b: 65 mm

Jaw height h_1 : 13.8 mm

Ring thickness h_2 : 17 mm

Ring \varnothing D: 60 mm

Ratchet torque rating: 795 N·m

Technical description

Ring \varnothing D	60 mm
Jaw height h_1	13.8 mm
Spanner length L	425 mm
Jaw width b	65 mm
Width across flats	30 mm
Ratchet torque rating	795 N·m
Ring thickness h_2	17 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner