


**Solid carbide jobber drill extra short, TiN, Ø DC h7: 0,5mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 122160 0,5    |
| GTIN         | 4045197040084 |
| Item class   | 12E           |

**Description**
**Version:**

**Similar to DIN 6539** (extra short).

Nominal Ø and shank Ø equal.

TiN coating.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Non slip clamping in drill chuck No. 341050 with diamond coated jaws.

**Technical description**

|  |               |
|--|---------------|
| Nominal Ø $D_c$                            | 0.5 mm        |
| Flute length $L_c$                         | 3 mm          |
| Feed $f$ in steel < 1100 N/mm <sup>2</sup> | 0.01 mm/rev.  |
| Number of cutting edges $Z$                | 2             |
| Shank tolerance                            | h7            |
| Tolerance nominal Ø                        | h7            |
| Shank Ø $D_s$                              | 0.5 mm        |
| Overall length $L$                         | 20 mm         |
| Standard                                   | DIN 6539      |
| recommended maximum drilling depth $L_2$   | 2.3 mm        |
| Coating                                    | TiN           |
| Tool material                              | Solid carbide |

|                 |                      |
|-----------------|----------------------|
| Type            | N                    |
| Point angle     | 118 degrees          |
| Helix angle     | 30 degrees           |
| Shank           | Parallel shank to h7 |
| Through-coolant | no                   |
| Colour ring     | without              |
| Type of product | Jobber drill         |

### User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu plastics                   | suitable only under restricted conditions | 230 m/min      | N        |
| Aluminium (short chipping)     | suitable                                  | 160 m/min      | N        |
| Alu > 10% Si                   | suitable                                  | 160 m/min      | N        |
| Steel < 500 N/mm <sup>2</sup>  | suitable                                  | 80 m/min       | P        |
| Steel < 750 N/mm <sup>2</sup>  | suitable                                  | 80 m/min       | P        |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  | 70 m/min       | P        |
| Steel < 1100 N/mm <sup>2</sup> | suitable                                  | 50 m/min       | P        |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  | 30 m/min       | P        |
| INOX < 900 N/mm <sup>2</sup>   | suitable only under restricted conditions | 30 m/min       | M        |
| INOX > 900 N/mm <sup>2</sup>   | suitable only under restricted conditions | 25 m/min       | M        |
| Ti > 850 N/mm <sup>2</sup>     | suitable                                  | 20 m/min       | S        |
| GG(G)                          | suitable                                  | 85 m/min       | K        |
| CuZn                           | suitable                                  | 160 m/min      | N        |
| Uni                            | suitable                                  |                |          |
| Oil                            | suitable                                  |                |          |
| wet maximum                    | suitable                                  |                |          |

dry

suitable only under  
restricted conditions