

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 08/07mm

Order data

Order number	260320 08/07
GTIN	4045197877734
Item class	21T

Description

Boring bar carbide 08/07 mm Shank $\varnothing D_s$: 8 mm
 ISO code toolholder: E08K SDQCR/L07
 Setting angle κ : 107.5 °
 suitable indexable insert: DC.. 0702..
 Minimum pre-drill $\varnothing D_{min}$: 12 mm
 Centre offset L_3 : 7 mm

Technical description

Clamping height L_2	7.6 mm
Centre offset L_3	7 mm
Overall length L	125 mm
Minimum pre-drill $\varnothing D_{min}$	12 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
ISO code toolholder	E08K SDQCR/L07
Insert size	7 mm
Setting angle κ	107.5 °
Shank $\varnothing D_s$	8 mm
Application type	right-hand
Boring depth up to	8xD

Tool material	Carbide
Standard	DIN 8024
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
Set of insert screws 10 pieces	269413
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8