

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 16/07mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 260344 16/07  |
| GTIN         | 4045197877949 |
| Item class   | 21T           |

**Technical description**

|  |                               |
|--|-------------------------------|
| suitable indexable insert                | DC.. 0702..                   |
| Overall length L                         | 180 mm                        |
| Centre offset L <sub>3</sub>             | 11 mm                         |
| Setting angle $\kappa$                   | 93 degrees                    |
| Pack of insert screws                    | 269028 7                      |
| Head length L <sub>1</sub>               | 33 mm                         |
| Insert size                              | 7 mm                          |
| Minimum pre-drill $\varnothing D_{\min}$ | 21 mm                         |
| ISO code toolholder                      | A16Q SDXCR/L07                |
| Clamping height L <sub>2</sub>           | 15 mm                         |
| Usable depth T                           | 4.3 mm                        |
| Shank $\varnothing D_s$                  | 16 mm                         |
| Standard                                 | Works standard                |
| Application type                         | right-hand                    |
| Boring depth up to                       | 3xD                           |
| Through-coolant                          | yes                           |
| Application                              | Internal longitudinal turning |

|                 |            |
|-----------------|------------|
| Type of product | Boring bar |
|-----------------|------------|

---

## Accessories

|  |            |
|--|------------|
| Set of insert screws Type 7  | 269028 7   |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8                             | 674248 TX8 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |