



## Torque analyser for torque wrenches "SmartCheck", maximum torque: 100 Nm



### Order data

Order number	654650 100
GTIN	4018754273010
Item class	63B

### Description

#### Version:

Variable and flexible torque tester with rotating display and base body. Can be mounted horizontally and vertically. The display and the membrane keypad is splash-proof and the body is made of impact resistant plastic.

3 operating modes:

- **Tracking display (track)**
- **Trigger point sensing (first peak)**
- **Peak value display (peak hold)**

**Units of measure:** N·m, lbf·ft, lbf·in.

#### Advantage:

Compact and variable torque analyser. Operation on power supply or batteries.

#### Application:

Adjusting **torque screwdrivers and torque wrenches** with or without setting scale.

#### Supplied with:

With power supply unit in a sturdy plastic case.

Calibration: O4

Torque measuring accuracy:  $\pm 1$  %

Measuring range: 10 - 100 Nm

Display unit width: 120 mm

Display unit height: 124 mm  
 Display unit depth: 167 mm  
 Weight: 5.31 kg  
 Square socket: 3/8 inch

## Technical description

Weight	5.31 kg
Display unit depth	167 mm
Square socket	3/8 inch
Display unit height	124 mm
maximum torque	100 Nm
Measuring range	10 - 100 Nm
Display unit width	120 mm
Torque measuring accuracy	±1 %
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Direction of tightening	For right and left-hand tightening
Test certificate	Manufacturer's test certificate
Calibration	O4

## Services

Calibration Torque analyser / sensor maximum torque 400/2 Nm	018860 400/2
DAkkS calibration Torque analyser / sensor maximum torque 1000/2 Nm	018840 1000/2