

KERN**Hanging scales type HCB, maximum weighing range: 100kg****Order data**

Order number	479435 100
GTIN	4045761030114
Item class	47D

Description**Version:**

- **Simple operation with 3 buttons.**
- **With tare button, attach empty container and set indication to zero.**
- **Hold button, the indication can be frozen for 5 seconds.**
- **Display unit switchable between kg, N and lb.**

Supplied with:

Stainless steel carabiner, stainless steel S-hook (non-standard for size 500 / 1000) and 3 batteries No.081561 size LR6.

Technical description

Body height	150 mm
Scale divisions	200 g
maximum weighing range	0 - 100 kg
Net weight	0.6 kg
Body width	80 mm

Body depth	45 mm
Calibration	K2
Number of batteries contained	3
Article no of the battery / rechargeable battery fitted	081561 LR6
Power supply	Battery-powered
Manufacturer's designation	HCB
Type of product	Suspended scales / crane scales

Services

Calibration Scales maximum weighing range 100 kg	027700 100
--	------------

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------