

KERN**Hanging scales type HCB, maximum weighing range: 200kg****Order data**

Order number	479435 200
GTIN	4045761030121
Item class	47D

Description**Version:**

- **Simple operation with 3 buttons.**
- **With tare button, attach empty container and set indication to zero.**
- **Hold button, the indication can be frozen for 5 seconds.**
- **Display unit switchable between kg, N and lb.**

Supplied with:

Stainless steel carabiner, stainless steel S-hook (non-standard for size 500 / 1000) and 3 batteries No.081561 size LR6.

Technical description

Net weight	0.6 kg
maximum weighing range	0 - 200 kg
Body height	150 mm
Scale divisions	500 g
Body width	80 mm

Body depth	45 mm
Calibration	Price on request
Article no of the battery / rechargeable battery fitted	081561 LR6
Number of batteries contained	3
Power supply	Battery-powered
Manufacturer's designation	HCB
Type of product	Suspended scales / crane scales

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------