

**Adapter for ratchet ring spanner, Type: 1****Order data**

Order number	614850 1
GTIN	4045197235800
Item class	62A

Description**Version:**

Hexagon shank with sprung ball or pressure piece for retention in the ring spanner. External square drive to DIN 3120, with ejector, to take sockets.

Advantage:

The adaptor converts a ratchet ring spanner size 10, 13 or 19 mm into a fully functioning ratchet.

Material:

Chrome vanadium steel, chrome-plated.

Suitable for :

Ratchet ring spanners No. 614800 – 614820, 614845 and 614870 – 614875 size 10 in each case.

Mounting AF: 10 mm

Square drive: 1/4 in

Technical description

Mounting AF	10 mm
Square drive	1/4 in
Material	Chrome vanadium steel

Surface	chrome-plated
Type of product	Square adapter

Accessories

Open ended spanner / ratchet ring spanner set, in a wallet with swivel head Number of keys 5	614814 5
Open ended spanner / ratchet ring spanner set, in a wallet Number of keys 4	614810 4
Spanner / ratchet ring spanner Width across flats 10 mm	614800 10
JOKER 6000 open ended spanners / ratchet ring spanners Width across flats 10 mm	614870 10
Open ended spanner / ratchet ring spanner set, in a wallet short version Number of keys 5	614818 5
Open ended spanner / ratchet ring spanner set, in a wallet Number of keys 5	614810 5
Open ended spanner / ratchet ring spanner set, in a wallet short version Number of keys 10	614818 10
Open ended spanner / ratchet ring spanner set, in a wallet Number of keys 10	614810 10
JOKER 6001 Switch open ended spanner / ratchet ring spanner, reversible, 15° offset Width across flats 10 mm	614875 10
Open ended spanner / ratchet ring spanner set, in a wallet with swivel head Number of keys 10	614814 10
Spanner / ratchet ring spanner with swivel head Width across flats 10 mm	614812 10
Spanner / ratchet ring spanner short version Width across flats 10 mm	614816 10
Double ratchet ring spanner, 15° offset Jaw widths 10X11 mm	614845 10X11
Spanner / ratchet ring spanner reversible 15° offset Width across flats 10 mm	614820 10