



## Adapter for ratchet ring spanner, Type: 3



### Order data

Order number	614850 3
GTIN	4045197235824
Item class	62A

### Description

#### Version:

Hexagon shank with sprung ball or pressure piece for retention in the ring spanner. External square drive to DIN 3120, with ejector, to take sockets.

#### Advantage:

The adaptor converts a ratchet ring spanner size 10, 13 or 19 mm into a fully functioning ratchet.

#### Material:

Chrome vanadium steel, chrome-plated.

#### Suitable for :

Ratchet ring spanners No. 614800 – 614820, 614845 and 614870 – 614875 size 19 in each case.

Mounting AF: 19 mm

Square drive: 1/2 in

### Technical description

Mounting AF	19 mm
Square drive	1/2 in
Material	Chrome vanadium steel

Surface	chrome-plated
Type of product	Square adapter

## Accessories

Open ended spanner / ratchet ring spanner set, in a wallet Number of keys 10	614810 10
Spanner / ratchet ring spanner short version Width across flats 19 mm	614816 19
Open ended spanner / ratchet ring spanner set, in a wallet Number of keys 4	614810 4
Double ratchet ring spanner, 15° offset Jaw widths 17X19 mm	614845 17X19
Open ended spanner / ratchet ring spanner set, in a wallet Number of keys 5	614810 5
Spanner / ratchet ring spanner Width across flats 19 mm	614800 19
JOKER 6001 Switch open ended spanner / ratchet ring spanner, reversible, 15° offset Width across flats 19 mm	614875 19
Spanner / ratchet ring spanner with swivel head Width across flats 19 mm	614812 19
Spanner / ratchet ring spanner reversible 15° offset Width across flats 19 mm	614820 19
Open ended spanner / ratchet ring spanner set, in a wallet with swivel head Number of keys 10	614814 10
JOKER 6000 open ended spanners / ratchet ring spanners Width across flats 19 mm	614870 19
Open ended spanner / ratchet ring spanner set, in a wallet short version Number of keys 10	614818 10