

**Garant****Double ratchet ring spanner, 15° offset, Jaw widths: 10X11mm****Order data**

Order number	614845 10X11
GTIN	4045197415882
Item class	61B

**Description****Version:**

Drop forged, with particularly free-running sturdy ratchet ring at each end. Reversible for left- and right-hand tightening. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

**Technical description**

maximum ring $\varnothing$ D2	23.1 mm
maximum ring $\varnothing$ D1	21.5 mm
Width across flats 1	10 mm
maximum ring height $h_2$	8.2 mm
Width across flats 2	11 mm
maximum ring height $h_1$	7.6 mm
overall length L	150 mm
Width across flats	metric
No. of teeth	5
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Type of product	Spanner

---

## Accessories

Adapter for ratchet ring spanner Type 1	614850 1
---	----------