

KERN**Crane scales type HFB, maximum weighing range: 300 kg****Order data**

| | |
|--------------|---------------|
| Order number | 479436 300 |
| GTIN | 4045761111660 |
| Item class | 47D |

Description**Version:**

Back-lit LCD display, easily read even from afar. Internal battery (with optical charge display) gives high mobility. Data hold function for retaining the display value.

Character height 25 mm with twin display at the rear. Battery lasts approx. 20 hours.

Supplied with:

Remote control with 2 batteries No. 081556 size LR3, mains adapter.

Attention:

German version. Order free UK adapter plug No. 08 1174_GB.

Calibration: Price on request

Scale divisions: 100 g

Error limit from maximum value: 2 %

Body width: 163 mm

Body depth: 126 mm

Body height: 159 mm

Overall length: 390 mm

Technical description

| | |
|------------|--------|
| Net weight | 2.2 kg |
|------------|--------|

| | |
|---|------------------|
| Body height | 159 mm |
| Overall length | 390 mm |
| maximum weighing range | 0 - 300 kg |
| Scale divisions | 100 g |
| Operating temperature | 0 - 40 °C |
| Error limit from maximum value | 2 % |
| Body width | 163 mm |
| Body depth | 126 mm |
| Calibration | Price on request |
| Number of batteries contained | 2 |
| Batteries / rechargeable batteries included | 081556 LR3 |
| Height of numerals | 25 mm |
| Manufacturer's designation | HFB |
| Battery working life | 20 h |

Services

| | |
|------------------------|--------|
| Labelling laser-etched | 018940 |
|------------------------|--------|

Accessories

| | |
|---|------------|
| Alkaline-manganese batteries International size LR3 | 081556 LR3 |
|---|------------|