



Double ratchet ring spanner, Widths across flats: 10X12mm



Order data

Order number	614843 10X12
GTIN	4045197879431
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths. Reversible for left- and right-hand tightening, plus centre position. With unequal jaw widths, deep cranked. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

Width across flats	metric
maximum ring height h_2	18 mm
maximum ring \varnothing D2	24 mm
maximum ring \varnothing D1	21.5 mm
Width across flats 2	12 mm
overall length L	197 mm
maximum ring height h_1	16 mm
Width across flats 1	10 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated

Ring end cranked	yes
Ratchet reversible	no
Type of product	Spanner

Accessories

Adapter for ratchet ring spanner Type 4	614850 4
---	----------