

## Garant

### Double-ended ring spanner, deeply cranked, Width across flats: 16X17 mm



#### Order data

Order number	615700 16X17
GTIN	4045197160690
Item class	61A

#### Description

##### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **AS drive** profile.

##### Advantage:

**AS drive** profile:

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

##### Standard:

**DIN 838 / ISO 3318**

##### Material:

Chrome vanadium steel, chrome-plated.

##### Note:

**AS-Drive** – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. All GARANT and STAHLWILLE deep cranked double-ended ring spanners are equipped with this profile – recognisable by the **AS drive** mark.

Spanner length L: 255 mm

maximum ring  $\varnothing$  D<sub>1</sub> max: 25 mm

maximum ring  $\varnothing$  D<sub>2</sub> max: 27 mm

#### Technical description

Spanner length L	255 mm
------------------	--------

maximum ring $\varnothing D_1$ max	25 mm
Width across flats 2	17 mm
maximum ring $\varnothing D_2$ max	27 mm
Width across flats 1	16 mm
Width across flats	metric
Type of product	Spanner