

Garant**Circular saw blade, wood, alternating teeth fine, Blade Ø D: 300mm****Order data**

Order number	584055 300
GTIN	4045197220837
Item class	51S

Description**Version:**

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

Application:

For circular, cross-cut, compound, and mitre saws.

Type KW for **board materials with facing veneer and plastic covered on both sides as well as surface treated materials** with the highest cut quality requirements.

Note:

Further circular saw blades can be found in Group 17.

Technical description

Number of teeth	72
Bore Ø	30 mm
Blade Ø D	300 mm
Width of cut B	3.2 mm

Drive holes number/Ø/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade