

**Garant**

**Circular saw blade, metal, alternating teeth with bevel universal, Blade Ø D: 300mm**

**Order data**

Order number	584095 300
GTIN	4045197220974
Item class	51S

**Description****Version:**

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

**Application:**

For circular, cross-cut, compound, and mitre saws.

**Universal** circular saw blade for cutting **a wide range of materials** such as **steel flats and angle sections**, aluminium and other non-ferrous metals. Flat teeth with bevel up to Ø 250 mm; alternating set with bevel from Ø 300 mm.

**Note:**

**Further circular saw blades can be found in Group 17.**

**Technical description**

Number of teeth	60
Bore Ø	30 mm
Blade Ø D	300 mm

Width of cut B	2.4 mm
Drive holes number/Ø/pitch circle	2/10/60 and 2/11/63 and 2/12/64 and 2/7/42 mm
Type of product	Circular saw blade