



Double-ended ring spanner, deeply cranked, chrome-plated, Width across flats: 20X22mm



Order data

Order number	615950 20X22
GTIN	4045197332219
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

maximum ring $\varnothing D_2$ max	34 mm
Width across flats 2	22 mm
Spanner length L	318 mm
Width across flats 1	20 mm
maximum ring $\varnothing D_1$ max	31 mm
Width across flats	metric
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

