

KERN
Precision scales, type PCB, maximum weighing range: 6000 g


Order data

Order number	479510 6000
GTIN	4045761084841
Item class	47D

Description

Version:

- **Robust plastic casing.**
- **Simple, self-explanatory 5-button operation.**
- **Selectable mains and battery operation. Attention: German version! Please order a GB adapter plug No. 08 1174_GB separately. Auto-off after 3 minutes.**
- **Calibration programme CAL: For accuracy adjustment (required external calibration weight available on request).**
- **Quantity counting: Reference quantities selectable 5, 10, 25, 50 pieces Display selectable between pieces and weight.**
- **Formulation weighing: Separate memory for weight of the tare vessel and of the formulation ingredients (net totals).**

Supplied with:

Mains adapter 230 V/ 50 Hz and protective hood.

Optional extras:

Battery No. 081561 size 6LR61; internal rechargeable battery on request. Data cable, printer on request.

Attention:

German version. Order free UK adapter plug No. 08 1174_GB.

Calibration: K2

Scale divisions: 1 g

Reproducibility: 1 g

Linearity: ± 2 g
 Settling time: 3 s
 Minimum unit weight: 20 g
 Dimensions of weighing plate: 150×170 mm

Technical description

Reproducibility	1 g
maximum weighing range	0 - 6000 g
Scale divisions	1 g
Net weight	2 kg
Linearity	± 2 g
Depth	245 mm
Settling time	3 s
Height	79 mm
Dimensions of weighing plate	150×170 mm
Manufacturer's designation	PCB
Minimum unit weight	20 g
Width	163 mm
Interface	RS232 interface
Calibration	K2
Type of product	Precision balance

Services

Calibration Spirit level maximum weighing range 50 kg	018920 50
Labelling laser-etched Type	018940
DAkkS calibration Spirit level maximum weighing range 50	019700 50

Accessories

Alkaline-manganese batteries International size 6LR61	081556 6LR61
---	--------------