



## Double-ended ring spanner, deeply cranked, phosphated, Width across flats: 24X26mm



### Order data

Order number	615900 24X26
GTIN	4045197329899
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.  
With oval shaft.

#### Standard:

**DIN 838 / ISO 3318**

#### Material:

Chrome vanadium steel, phosphated.

### Technical description

Width across flats 2	26 mm
maximum ring $\varnothing D_1$ max	36 mm
maximum ring $\varnothing D_2$ max	40 mm
Spanner length L	337 mm
Width across flats 1	24 mm
Width across flats	metric
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

