

GECHTER**Hand lever toggle press, Type: 16****Order data**

Order number	086760 16
GTIN	2050001743749
Item class	08V

Description**Version:**

Sturdy, hollow cast body with large base. Base with 4 holes for attachment to workbench etc. The press tool carriage runs without play on dovetail guides and is adjustable for height. Additionally the press stroke (ram stroke) can also be set by an adjusting screw to give the desired vertical lift. The table has a 10 mm T-slot for attaching clamps. The lever bolt can be moved to give varying forces and different stroke lengths (see table).

Application:

For embossing, riveting, upsetting, and punching as well as for bending, compressing, and pressing in bushes etc.

Colour:

Light grey RAL 7035.

Note:

Hand lever presses with air support available in the online shop under No. 086761.

Technical description

Stroke length long	0 - 58 mm
Force for long stroke	24 kN

T-slot to DIN 650	2 pcs. size 10
Weight	79 kg
Throat	160 mm
Table depth	230 mm
Installation height	100 - 320 mm
Mounting hole in the slide ram	15 H 7 mm
Stroke length short	0 - 25 mm
Type	16
Force for short stroke	32 kN
Footprint width	300 mm
Footprint depth	420 mm
Table width	325 mm
Height without hand lever	710 mm
Type of product	Toggle lever press