

**Double-ended ring spanner, deeply cranked, phosphated, Width across flats: 12X14mm****Order data**

Order number	615900 12X14
GTIN	4045197385390
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

maximum ring $\varnothing D_1$ max	20 mm
Width across flats 2	14 mm
maximum ring $\varnothing D_2$ max	23 mm
Spanner length L	216 mm
Width across flats 1	12 mm
Width across flats	metric
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

