

Garant GRIDLINE

ToolTruck mobile workbench with full extension drawers, 20×16G, Number of drawers: 6



Order data

Order number	914560 6
GTIN	4045197892249
Item class	9GT

Description

Version:

The ToolTruck mobile workbench has a worktop of X-ABS for highly demanding technical applications. Cupboard with **2 storage shelves** and door. **Cabinet stiles are clad with LDPE bumpers.**

Central locking locks the door of the cupboard and drawers at the same time.

Fitted with:

Drawer front height: 75; 75; 75; 125; 200; 200 mm

Supplied with:

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75,

each 125 mm drawer 1 slotted partition No. 951510 size 125.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Note:

Optional storage shelf / side compartment No. 914791 not integrated into the ToolTruck central locking system, locked instead by a separate cylinder lock.

For drawers of height 200 mm, more suitable components now include slotted dividers No. 951510 size 200, edge partitions No. 951560 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951560 size 75; size 125 and size 200;

Slotted dividers No. 951510 size 75; size 125 and size 200;
 Divider inserts No. 951721 – 951821 size 75; No. 951731 – 951821 size 125 and No. 951741 – 951821 size 200.

Cylinder lock: modular lock barrel

Individual drawer release system: One-hand

Drawer usable area in G: 20×16

Height: 1000 mm

Width: 1195 mm

Depth: 500 mm

Drawer usable width: 500 mm

Drawer usable depth: 400 mm

Drawer usable width in G: 20

Technical description

Width	1195 mm
Depth	500 mm
Drawer usable depth	400 mm
Height	1000 mm
Drawer usable width	500 mm
Number of drawers	6
Weight	94.4 kg
Drawer usable width in G	20
Drawer usable depth in G	16
Drawer usable area in G	20×16
Series	ToolTruck mobile workbench
Series	ToolTruck
Individual drawer release system	One-hand
Configurator relevant	yes
Drawer/pull-out shelf load capacity	40 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular lock barrel

Product name attribute	20×16G
Type of product	mobile workbench

Accessories

Slotted dividers Depth 16G suitable for drawer front height 125 mm	951510 125
Slotted dividers Depth 16G suitable for drawer front height 75 mm	951510 75
Storage shelf fixed Type 1	914774 1
Set of wheels for roller cabinets and mobile workbenches Type G	915567 G
Lock plate for GridLine Type VA21	914227 VA21