

**Cordless inspection camera, Manufacturer's designation: M12IC****Order data**

Order number	492712 M12IC
GTIN	4002395001910
Item class	03L

Description**Version:**

Compact cordless inspection camera for visual inspection of places that are difficult to access.

- **69 mm / 2.7 inch rotatable colour LCD display.**
- **Automatic contrast compensation and white balance.**
- **Waterproof camera head with 3-step LED illumination.**
- **Flexible watertight camera cable (0.9 m long).**
- **Digital zoom for better detection of details.**

Supplied with:

Supplied with 1× 12 V / 2.0 Ah Li-ion battery, charger, camera cable, hook, magnet, mirror, carrying case.

Packaging: Carrying case

Battery voltage: 12 V

Battery capacity: 2 A·h

Display size: 2.7 in

Display resolution: 320×240 px

Camera head Ø: 9 mm

Length of the camera cable: 900 mm

Technical description

Display resolution	320×240 px
Manufacturer's designation	M12 IC
Length of the camera cable	900 mm
Display size	2.7 in
Battery voltage	12 V
Battery capacity	2 A·h
Camera head Ø	9 mm
Weight	0.66 kg
Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	Carrying case
Type of product	Endoscope