



## Double-ended ring spanner, shallow cranked, Width across flats: 14X15mm



### Order data

Order number	616500 14X15
GTIN	4018754021734
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths. Thin, flat rings for use in restricted places. With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Shallow cranked head at each end. With **AS-Drive** profile.

#### Standard:

**DIN 897 / ISO 3318**

#### Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

### Technical description

Width across flats 2	15 mm
maximum ring height $h_{1 \max}$	11.5 mm
Width across flats 1	14 mm
maximum ring $\varnothing D_1 \max$	20.1 mm
maximum ring $\varnothing D_2 \max$	21.4 mm
Spanner length L	219 mm
Width across flats	metric
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chromium-plated over nickel
Type of product	Spanner

