



## Double-ended ring spanner, deeply cranked, chrome-plated, Width across flats: 41X46mm



### Order data

Order number	615950 41X46
GTIN	4045197441812
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.  
With oval shaft.

#### Standard:

**DIN 838 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

Width across flats 2	46 mm
Spanner length L	475 mm
maximum ring $\varnothing D_2$ max	67 mm
maximum ring $\varnothing D_1$ max	60 mm
Width across flats 1	41 mm
Width across flats	metric
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

