

HOLEX**Double-ended ring spanner, deeply cranked, chrome-plated, Width across flats: 25X28mm****Order data**

Order number	615950 25X28
GTIN	4045197441782
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

maximum ring $\varnothing D_2$ max	40 mm
Spanner length L	346 mm
maximum ring $\varnothing D_1$ max	36 mm
Width across flats 1	25 mm
Width across flats 2	28 mm
Width across flats	metric
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

