


**Garant****Diamond grinding points brazed D427, D, Type: ZY4004****Order data**

Order number	552750 ZY4004
GTIN	4045197880888
Item class	51E

**Description****Version:**

Precision-ground blanks with **diamond application** in **vacuum brazing processes**.

**Advantage:**

- **More free-cutting than galvanically bonded grinding points due large grit projection (about 70% of the grit projects from the bonding material) and stronger bonding.**
- **The open structure and coarse D427 grit reduce the grinding temperature and minimise the tendency to clog up.**

**Application:**

For hand-held use, on industrial robots or CNC grinding machines for **rough grinding work** with high material removal rates. **Side milling, contour milling** of composite materials (CRP/GRP), fibreglass, graphite, honeycomb.

**Note:**

Other grit grade, special shapes or grinding points with internal cooling for stationary use are available in request.

Grinding medium code: D

Shape description: Disc

Head Ø: 40 mm

Head length: 3.5 mm

Overall length: 50 mm

Shank Ø: 6 mm

## Technical description

Shank Ø	6 mm
Overall length	50 mm
Head Ø	40 mm
Shape description	Disc
Head length	3.5 mm
Grinding media	Diamond
Grinding medium code	D
Type of product	Grinding point

## User data

	Suitability	V <sub>c</sub>	ISO code
Plastic, GRP	suitable	15-20 m/s	
Stone	suitable	15-20 m/s	
wet maximum	suitable		
dry	suitable only under restricted conditions		