



Double-ended ring spanner set, straight, Number of keys: 8



Order data

| | |
|--------------|---------------|
| Order number | 617610 8 |
| GTIN | 4018754085231 |
| Item class | 63A |

Description

Version:

Drop-forged. With close tolerance jaw widths.

STAHLWILLE – With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Thin, flat rings for use in restricted places. With **AS Drive** profile.

Standard:

DIN 837 B / ISO 3318

Material:

STAHLWILLE – Chrome alloy steel; non-flaking chrome-plated over nickel; smoothed finish surface.

Content:

1 each double-ended ring spanner No. 617600 / 617950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×21; 19×22

Technical description

| | |
|--------------------|---------|
| Number of keys | 8 |
| Width across flats | metric |
| Type of product | Spanner |

Accessories

| | |
|---|--------------|
| Double-ended ring spanner, straight Width across flats 16X17 mm | 617600 16X17 |
| Double-ended ring spanner, straight Width across flats 8X9 mm | 617600 8X9 |
| Double-ended ring spanner, straight Width across flats 18X21 mm | 617600 18X21 |
| Double-ended ring spanner, straight Width across flats 10X11 mm | 617600 10X11 |
| Double-ended ring spanner, straight Width across flats 19X22 mm | 617600 19X22 |
| Double-ended ring spanner, straight Width across flats 14X15 mm | 617600 14X15 |
| Double-ended ring spanner, straight Width across flats 6X7 mm | 617600 6X7 |
| Double-ended ring spanner, straight Width across flats 12X13 mm | 617600 12X13 |