



LED cordless work lamp, Type: MINIMAG

Order data

Order number	081516 MINIMAG
GTIN	5708997354032
Item class	08C

Description

Version:

LED cordless work lamp with high-power LEDs for high light output. With fold-out swivel support hook and powerful attachment magnet. Size STAR without suspension hook. Compact pocket-size torch of the MAG generation. Cordless work lamp and torch in one. With spotlight and main beam.

Standard:

- **LED cordless work lamp with high intensity LED.**
- **Compact torch format lamp.**
- **With spotlight and main beam.**

Supplied with:

USB charging cable, 3.7 V / 1.2 Ah Li-ion battery.

IP Index of Protection: IP 20

Illumination step 1: 120 lm

Illumination step 2: 50 lm

Energy efficiency class : A

Working life: 4 h

Lamp body length: 202 mm

Lamp body width: 40 mm

Technical description

Type of product