



Double-ended open ring spanner, Width across flats: 8X10mm



Order data

Order number	619200 8X10
GTIN	4018754021888
Item class	63A

Description

Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With easy-grip fluted shaft. Optimum flexural strength, good torque transmission, very light and easy to use. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

Standard:

DIN 3118 / ISO 3318

Material:

Chrome alloy steel; non-flaking, chrome-plated over nickel.

Technical description

maximum ring height $h_{2\max}$	8.5 mm
Width across flats 2	10 mm
maximum ring $\varnothing D_1 \max$	17.5 mm
maximum ring height $h_{1\max}$	7 mm
Width across flats 1	8 mm
maximum ring $\varnothing D_2 \max$	19.5 mm
Spanner length L	145 mm
Width across flats	metric
Standard	DIN 3118 / ISO 3318
Ring setting	10 degrees

Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated (non-flaking)
open ring	yes
Type of product	Spanner