



Double-ended crescent ring spanner, Jaw widths: 14X17mm



Order data

Order number	618000 14X17
GTIN	4018754022069
Item class	63A

Description

Version:

Drop forged ring spanner in a crescent shape. Close tolerance jaw widths. Torsion-resistant fluted shaft. With **AS Drive** profile.

Application:

Specially for working on engine blocks, e.g. fitting carburettors, alternators etc. and everywhere where nuts and bolts are difficult to reach using normal ring spanners.

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish surface (no sharp edges).

Technical description

Width across flats 2	17 mm
Ring \varnothing D ₂	24.5 mm
Ring \varnothing D ₁	21 mm
Width across flats 1	14 mm
Wrench length	179 mm
Width across flats	metric
Head height h	7.5 mm
Manufacturing process	drop forged
Material	Chrome alloy steel

Surface	chrome-plated (non-flaking)
Ring end AS drive	yes
Crescent shape	yes
Type of product	Spanner