

**Bench grinding wheel D×T×H (mm), 125×20×32, Type: C800****Order data**

Order number	596100 C800
GTIN	9003170100168
Item class	53Y

**Description****Version:**

**Resiliently bonded honing wheels**, very soft. Maximum working speed 25 m/s.

**Application:**

For sharpening of cutting, polishing, effect grinding and fine deburring work. The clamping flange diameter area must be at least 2/3 of the wheel diameter.

**Specification:**

**PU-bonded silicon carbide.**

**Supplied with:**

Reducing ring set for the indicated bores.

**Note:**

For compact deburring wheels see No. 568725 ff.

**Technical description**

Grit designation	extra fine
Grit	800
Grinding medium code	SiC

maximum circumferential speed	25 m/s
Specification	PU-bonded silicon carbide
Grinding media	Silicon carbide (SiC)
Grinding process	Bench grinder
Reducing ring inner Ø	25 mm
Reducing ring inner Ø	20 mm
Reducing ring inner Ø	16 mm
Shape	1
Disc Ø D	125 mm
Disc thickness T	20 mm
Product name attribute	125×20×32
Bore Ø H	32 mm
Type of product	Grinding wheel for off-hand grinders

---

## Accessories

Reducing ring set for the natural bore of the grinding wheel 32 mm	596000 32
--	-----------