

**Aluminium Oxide (A) finishing belt KK711X, 120×1500 mm, Grit: 60****Order data**

| | |
|--------------|---------------|
| Order number | 558050 60 |
| GTIN | 4018875090756 |
| Item class | 56V |

Description**Version:**

Universal finishing belt with **Aluminium Oxide(A)**. The grinding medium underlay is optimally designed to the grit and type of finishing belt.

Robust X-fabric for **high material removal rate** on stationary grinding machines.

Application:

For universal use on all popular materials: **steel**, non-ferrous metals, cast iron, **aluminium alloys**, **wood**.

Note:

Other grit sizes, qualities, and dimensions are available on request in line with the manufacturer's minimum order quantities. Unless specified otherwise on the order, belts will be supplied with standard joints. See No. 568526ff for spare finishing belts for burnishing machines.

Technical description

| | |
|----------------------|--------|
| Grit | 60 |
| Series | KK711X |
| Grinding medium code | A |

| | |
|---|----------------|
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Linishing belt width | 120 mm |
| Linishing belt length | 1500 mm |
| Product name attribute | 120×1500 mm |
| Type of product | Linishing belt |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | 35-40 m/s | |
| Steel < 900 N/mm ² | suitable | 32-38 m/s | P |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | 20-25 m/s | P |
| Steel < 55 HRC | suitable only under restricted conditions | 32-38 m/s | H |
| INOX | suitable only under restricted conditions | 18-30 m/s | |
| Ti | suitable only under restricted conditions | 10-20 m/s | |
| GG(G) | suitable only under restricted conditions | 30-45 m/s | K |
| CuZn | suitable | 35-45 m/s | N |
| Plastic, GRP | suitable | 10-30 m/s | |
| Wood | suitable | 23-26 m/s | |
| dry | suitable | | |