


**Bench grinding wheel D×T×H (mm), 175×25×51, Type: SC80****Order data**

Order number	596350 SC80
GTIN	9003170096539
Item class	53Y

**Description****Version:**

**High-quality long-lasting bench grinder wheels** in ceramic bonding. Very low radial and axial run-out, maximum cutting speed 40 m/s. For **general use** on double-ended bench grinding machines for deburring, sharpening and resharpening tools.

**Application:**

For sharpening solid carbide and carbide-tipped tools as well as cast iron and tungsten components.

**Specification:**

Green **silicon carbide**, hardness grade J.

**Supplied with:**

Reducing ring set for the indicated bores.

**Note:**

For compact deburring wheels see No. 568725 ff.

**Technical description**

Grit designation	fine
Grit	80

Grinding medium code	SiC
maximum circumferential speed	40 m/s
Specification	Green silicon carbide, hardness grade J
Grinding media	Green Silicon Carbide
Grinding process	Bench grinder
Reducing ring inner Ø	32 mm
Shape	1
Disc Ø D	175 mm
Disc thickness T	25 mm
Product name attribute	175×25×51
Bore Ø H	51 mm
Type of product	Grinding wheel for off-hand grinders

---

## Accessories

Reducing ring set for the natural bore of the grinding wheel 51 mm	596000 51
--	-----------