

**Bench grinding wheel D×T×H (mm), 300×40×76, Type: SC80****Order data**

Order number	596610 SC80
GTIN	9003170014267
Item class	53Y

Description**Version:**

Shape 5 with single-sided recess 125×20 mm. **High-quality long-lasting bench grinder wheels** in ceramic bonding. Very low radial and axial run-out, maximum cutting speed 40 m/s. For **general use** on double-ended bench grinding machines for deburring, sharpening and resharpening tools.

Application:

For sharpening solid carbide and carbide-tipped tools as well as cast iron and tungsten components.

Specification:

Green **silicon carbide**, hardness grade J.

Supplied with:

Reducing ring set for the indicated bores.

Note:

For compact deburring wheels see No. 568725 ff.

Technical description

Grit designation	fine
------------------	------

Grit	80
Grinding medium code	SiC
maximum circumferential speed	40 m/s
Specification	Green silicon carbide, hardness grade J
Grinding media	Green Silicon Carbide
Grinding process	Bench grinder
Reducing ring inner Ø	51 mm
Reducing ring inner Ø	40 mm
Shape	5
Disc Ø D	300 mm
Disc thickness T	40 mm
Product name attribute	300×40×76
Bore Ø H	76 mm
Type of product	Grinding wheel for off-hand grinders

Accessories

Reducing ring set for the natural bore of the grinding wheel 76 mm

596000 76