



## Angle polisher WPO, Type: 72214950



### Order data

Order number	077712 72214950
GTIN	4014586862743
Item class	03F

### Description

#### Version:

- **Stepless electronic speed control for optimum tool use.**
- **With spigot also applicable as a fully functional burnishing machine for longitudinal jobs.**
- **Very high speed stability at any load over the entire range.**
- **Automatic start inhibit against uncontrolled restart after power supply interruption.**

#### Supplied with:

Fein angle polisher WPO 14-25E, side handle. 1 carrying case, 1 arm (adjustable), safety bar, spigot for rollers and multi-spline rollers (100 mm), resilient abrasive roller, (100×100 mm, 60 grit), lamellar fleece roller (100×100 mm, 180 grit), hook and loop backing pad (Ø 115 mm, M14), 1 abrasive fleece with folds 30×150 mm, spigot 15 - 50 mm, 10 hook and loop abrasive fleeces (Ø 115 mm fine).

#### Optional extras:

Standard surface finish set, No. 077718 size F, burnishing set for profiles, No. 077718 size S, polishing set, No. 077718 size P, pipework set, No. 077718 size R.

### Technical description

Power consumption	1200 W
Manufacturer's designation	WPO starter set – stainless steel
Weight	2.4 kg

Toolholder	M14
maximum polishing tool Ø	250 mm
maximum vibration to EN	3.5 m/s <sup>2</sup>
Speed range	900 - 2500 min <sup>-1</sup>
Packaging	Carrying case
Power supply	Mains operated
Type of product	Polishing machine

---

## Accessories

Stainless steel set for WPO angle polisher Type S	077718 S
Stainless steel set for WPO angle polisher Type F	077718 F
Stainless steel set for WPO angle polisher Type R	077718 R