

**Bench grinding wheel D×T×H (mm), 175×25×51, Type: C800****Order data**

Order number	596350 C800
GTIN	9003170520874
Item class	53Y

Description**Version:**

Resiliently bonded honing wheels, very soft. Maximum working speed 25 m/s.

Application:

For sharpening of cutting, polishing, effect grinding and fine deburring work. The clamping flange diameter area must be at least 2/3 of the wheel diameter.

Specification:

PU-bonded silicon carbide.

Supplied with:

Reducing ring set for the indicated bores.

Note:

For compact deburring wheels see No. 568725 ff.

Technical description

Grit	800
Grit designation	extra fine
Grinding medium code	SiC

maximum circumferential speed	25 m/s
Specification	PU-bonded silicon carbide
Grinding media	Silicon carbide (SiC)
Grinding process	Bench grinder
Reducing ring inner Ø	32 mm
Shape	1
Disc Ø D	175 mm
Disc thickness T	25 mm
Product name attribute	175×25×51
Bore Ø H	51 mm
Type of product	Grinding wheel for off-hand grinders

Accessories

Reducing ring set for the natural bore of the grinding wheel 51 mm

596000 51