

**Bench grinding wheel D×T×H (mm), 200×25×51, Type: NK60****Order data**

Order number	596400 NK60
GTIN	9003177183614
Item class	53Y

**Description****Version:**

**High-quality long-lasting bench grinder wheels** in ceramic bonding. Very low radial and axial run-out, maximum cutting speed 40 m/s. For **general use** on double-ended bench grinding machines for deburring, sharpening and resharpening tools.

**Application:**

For construction steels and low-alloy steels and also grey cast iron.

**Specification:**

Grey-blue **standard aluminium oxide**, hardness grade M

**Supplied with:**

Reducing ring set for the indicated bores.

**Note:**

For compact deburring wheels see No. 568725 ff.

**Technical description**

Grit designation	medium
Grit	60

Grinding medium code	A
maximum circumferential speed	40 m/s
Specification	Grey-blue standard aluminium oxide, hardness grade M
Grinding media	Grey-blue Aluminium Oxide
Grinding process	Bench grinder
Reducing ring inner Ø	32 mm
Shape	1
Disc Ø D	200 mm
Disc thickness T	25 mm
Product name attribute	200×25×51
Bore Ø H	51 mm
Type of product	Grinding wheel for off-hand grinders

---

## Accessories

Reducing ring set for the natural bore of the grinding wheel 51 mm

596000 51