

**Endoscope probe, flexible, 5.5 mm Ø, Probe length: 1000mm****Order data**

Order number	492937 1000
GTIN	4045197894540
Item class	42L

Description**Version:**

Sturdy watertight probe head (IP67) of stainless steel with dimmable white LEDs. Direction of view 0°.

Probe particularly resistant over its entire length due to metal mesh protective sleeve.

Particularly suitable for sharp-edged cast iron parts. Very flexible. Image aperture angle 90°.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Ideal for inspection of voids where access is difficult, e.g. **automotive:** Engine, gearbox, fuel tank, bodywork, dashboard, appraisal. **Aerospace:** engines, turbines, pipework, and wiring systems. **Buildings:** Assessment of the structure of buildings, water damage, pest infestation.

Pipework systems: weld seams, traces of foreign bodies, leaks. **Hydraulic systems:** cylinders, leaks. **Heating - sanitation - air conditioning:** ovens, furnaces, boilers, air conditioning systems, drainage systems. **Pest control:** Bees' nests, wasps' nests, birds' nests, insect entry points. **Police, customs:** Vehicle checking, goods checking.

Suitable for:

All endoscope versions No. 492923; 492924; 492925; 492928.

Note:

Other types of probe (up to 30 m) with other probe head Ø and directions of view available on request.

Technical description

IP Index of Protection	IP 67
Camera resolution	640×480 px
Product name attribute	5.5 mm Ø

Type of product

Probe