


**Garant****Flap wheel (CER), 120 grit, Head Ø×head width: 30X10mm****Order data**

Order number	554170 30X10
GTIN	4045197882820
Item class	51E

**Description****Version:**

Flap strips bonded on to the shank of the tool.  
Abrasive strips covered with **ceramic grit (CER)**.

**Application:**

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

**Technical description**

maximum speed	25400 min <sup>-1</sup>
recommended speed	16000 min <sup>-1</sup>
Head width	10 mm
Shank Ø	6 mm
Head Ø	30 mm
Grit	120
Grinding media	Ceramic grit (CER)

Grinding medium code	Ceramic
Product name attribute	120 grit
Type of product	Flap wheel

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		