

**Diamond dished grinding wheel D×T×H (mm), 125×25×20, Type: D126****Order data**

Order number	597720 D126
GTIN	9003177423116
Item class	53Y

**Description****Version:**

**Cup grinding wheels and dished grinding wheels with diamond abrasive coating.**

General-purpose grit for medium to fine surface quality and very good metal removal rates.

**Specification: D126C75B DIAGO W-Carbide.**

**Application:**

**For general use on all common tool grinding machines.** For grinding **carbide tools and short chipping non-ferrous materials.** Very well suited to dry grinding, but can also be used for wet grinding.

**Technical description**

Grit	D126
Specification	D126C75B DIAGO W-Carbide
Grinding medium code	D
Grinding process	Tool grinding
Grinding media	Diamond

Shape	12A2D
Disc Ø D	125 mm
Disc thickness T	25 mm
Product name attribute	125×25×20
Bore Ø H	20 mm
Abrasive coating width W end face	10 mm
Abrasive coating height X	3 mm
Type of product	Sanding pad

### User data

	Suitability	V <sub>c</sub>	ISO code
Carbide (HM)	suitable		
Plastic, GRP	suitable only under restricted conditions		
wet maximum	suitable only under restricted conditions		
dry	suitable		